

●アプリケーション

合金種類	組成	板 材	板 材	テーブ材	テーブ材	円 盤	ブランク	ワイヤー	棒	管	ターゲ	電極	塩
		光沢・製地 仕上げ	光沢・製地 仕上げなし	光沢・製地 仕上げ	光沢・製地 仕上げなし	食卓用 食器類	コイン ・メダル	機械 ・ 設備 管理 ・ 医療 ・ 計測 ・ 制御 ・ 蒸発 プロセス	工業 ・ 電子 材料 ・ 接点 ・ ケーブル	光データ 記憶 ・ 電子 工学 ・ ガラス コーテ ィング ・ R&D	電気 めっき	電気 めっき	
		重量% ^{*)}											
純銀	Ag 4N	Ag ≥ 99.99	●	●	●	●	●	●	●	●	●	●	●
純銀	Ag 3N7	Ag ≥ 99.97	●	●	●	●	●	●	●	●	●	●	●
純銀	Ag 4N200	Ag ≥ 99.97/200-300ppmCu	●	●	●	●	●	●	●	●	●	●	●
純金		Au ≥ 99.99	●	●	●	●	●	●	●	●	●	●	●
純プラチナ		Pt ≥ 99.5	●	●	●	●	●	●	●	●	●	●	●
純パラジウム		Pd ≥ 99.5	●	●	●	●	●	●	●	●	●	●	●
AgNi0.15			●	●	●	●	●	●	●	●	●	●	●
AgNi0.2Mg0.22			●	●	●	●	●	●	●	●	●	●	●
Ag 970	AgCu3	Ag 97.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
Ag 935		Ag 93.5; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
Ag 925	スターリングシルバー	Ag 92.5; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
Ag 900	AgCu10	Ag 90.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
Ag 835		Ag 83.5; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
Ag 800	AgCu20	Ag 80.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
Ag 500	AgCu50	Ag 50.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
CuAg2		Ag 2.0; Cu 98.0	●	●	●	●	●	●	●	●	●	●	●
AgCdO 900/100	AgCdO10		●	●	●	●	●	●	●	●	●	●	●
AgNi 900/100	AgNi10	Ag 90.0; Ni 10.0	●	●	●	●	●	●	●	●	●	●	●
AgNi 800/200	AgNi20	Ag 80.0; Ni 20.0	●	●	●	●	●	●	●	●	●	●	●
AgCu1.5Ni0.15			●	●	●	●	●	●	●	●	●	●	●
AgPd 700/300	AgPd30	Ag 70.0; Pd 30.0	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド Au 986/-		Au 98.6; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
AuNi 950/50 カラーゴールド 950/50	AuNi5	Au 95.0; Ni 5.0	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド Au900/50		Au 90.0; Ag 5.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド 750/150 [淡黄色]		Au 75.0; Ag 15.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド 750/125 [山吹色]		Au 75.0; Ag 12.5; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド 750/90 [ローズ]		Au 75.0; Ag 9.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド 750/40 [赤]		Au 75.0; Ag 4.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
AuAgNi 710/260	AuAg26Ni3	Au 71.0; Ag 26.0; Ni 3.0	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド 585/200 [黄]		Au 58.5; Ag 20.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド 585/415 [淡黄色]		Au 58.5; Ag 41.5	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド 375/75		Au 37.5; Ag 7.5; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
カラーゴールド 333/75		Au 33.3; Ag 7.5; 残り Cu	●	●	●	●	●	●	●	●	●	●	●
Pd 850	PdCu15	Pd 85.0; 残り Cu	●	●	●	●	●	●	●	●	●	●	●

上記以外の合金についてはご相談に応じます。

^{*)} 含有量の公差は造幣局での検定試験に準じるものです。